

# Вытяжка для культивирования тканей 820-TCH

## Технические характеристики

По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04  
Ангарск (3955)60-70-56  
Архангельск (8182)63-90-72  
Астрахань (8512)99-46-04  
Барнаул (3852)73-04-60  
Белгород (4722)40-23-64  
Благовещенск (4162)22-76-07  
Брянск (4832)59-03-52  
Владивосток (423)249-28-31  
Владикавказ (8672)28-90-48  
Владимир (4922)49-43-18  
Волгоград (844)278-03-48  
Вологда (8172)26-41-59  
Воронеж (473)204-51-73  
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06  
Ижевск (3412)26-03-58  
Иркутск (395)279-98-46  
Казань (843)206-01-48  
Калининград (4012)72-03-81  
Калуга (4842)92-23-67  
Кемерово (3842)65-04-62  
Киров (8332)68-02-04  
Коломна (4966)23-41-49  
Кострома (4942)77-07-48  
Краснодар (861)203-40-90  
Красноярск (391)204-63-61  
Курск (4712)77-13-04  
Курган (3522)50-90-47  
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13  
Москва (495)268-04-70  
Мурманск (8152)59-64-93  
Набережные Челны (8552)20-53-41  
Нижний Новгород (831)429-08-12  
Новокузнецк (3843)20-46-81  
Ноябрьск (3496)41-32-12  
Новосибирск (383)227-86-73  
Омск (3812)21-46-40  
Орел (4862)44-53-42  
Оренбург (3532)37-68-04  
Пенза (8412)22-31-16  
Петрозаводск (8142)55-98-37  
Псков (8112)59-10-37  
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15  
Рязань (4912)46-61-64  
Самара (846)206-03-16  
Санкт-Петербург (812)309-46-40  
Саратов (845)249-38-78  
Севастополь (8692)22-31-93  
Саранск (8342)22-96-24  
Симферополь (3652)67-13-56  
Смоленск (4812)29-41-54  
Сочи (862)225-72-31  
Ставрополь (8652)20-65-13  
Сургут (3462)77-98-35  
Сыктывкар (8212)25-95-17  
Тамбов (4752)50-40-97  
Тверь (4822)63-31-35

Тольятти (8482)63-91-07  
Томск (3822)98-41-53  
Тула (4872)33-79-87  
Тюмень (3452)66-21-18  
Ульяновск (8422)24-23-59  
Улан-Удэ (3012)59-97-51  
Уфа (347)229-48-12  
Хабаровск (4212)92-98-04  
Чебоксары (8352)28-53-07  
Челябинск (351)202-03-61  
Череповец (8202)49-02-64  
Чита (3022)38-34-83  
Якутск (4112)23-90-97  
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: [pbf@nt-rt.ru](mailto:pbf@nt-rt.ru) || сайт: <https://plas-labs.nt-rt.ru/>

# GERMICIDAL WORKSTATION

## (STILL AIR ENCLOSURE)

Our catalog #820-TCH Workstation has been designed to fit nicely on a lab counter top. It provides simple protection when a more sophisticated device is not required. It is an ideal enclosure for many acute and simple research procedures.

Its modest weight of 60 pounds (27.5 Kg) makes it readily transportable. The main housing is formed of one (1) piece clear acrylic and offers total viewing of your task at hand. High impact clear PETG units or amber “light sensitive” units are also available.

This Workstation can also be used as a PCR Chamber or Tissue Culture Hood.

Features included with the product:

- Standard twenty-four (24) month warranty (Not consumables).
- Formed one (1) piece clear acrylic top section .375” (950 mm) thick. With “easy clean” corners.”
- “Bright Light” illumination system (40,000 hour lamp guarantee).
- Formed in place liquid barrier to facilitate easy clean up of spills.
- The U.V. system is rated at 254 nm. Automatic timer is included. Beta ray protected but not gamma rays.
- All controls are illuminated and the system is fused for safety.
- Ground key cock valve for introduction of Oxygen or your inert gas of choice.
- Formed plastic bottom with “spill guard.” This for easy clean up.
- Hospital grade multiple electric outlet strip (socket).
- Easy access sash. Iris diaphragms included.

Electrical requirements.

North American 115-120 Volts, 60 Hz. 12 Amps.  
Export Models 220-240 Volts, 50 Hz. Amps will vary as to the end users country.

#820-TCH Specifications


|                          |                                                  |
|--------------------------|--------------------------------------------------|
| I.D.                     | 41”w x 28”d x 17”h<br>1,040 mm x 710 mm x 432 mm |
| O.D. (w/Flange)          | 44”w x 29”d x 30”h<br>1,118 mm x 736 mm x 762 mm |
| Sash Opening             | 8.5” h x 27.5 long<br>216 mm x 700 mm            |
| Shipping Weight (Crated) | 110 Pounds<br>50 Kilos                           |



#820- TCH Germicidal Workstation  
#820- TCH/EXP Workstation (Export Model)



Workstation Sash for Draft Control  
featuring Iris Diaphragms.



Optional Workstation Vent #800-VENT/OUTLET

Catalog #800-VENT/OUTLET can be mounted just about anywhere on the enclosure and is available in any diameter. Use this to connect to your house exhaust system. Standard diameter is 4”Ø (102 mm).



По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04  
Ангарск (3955)60-70-56  
Архангельск (8182)63-90-72  
Астрахань (8512)99-46-04  
Барнаул (3852)73-04-60  
Белгород (4722)40-23-64  
Благовещенск (4162)22-76-07  
Брянск (4832)59-03-52  
Владивосток (423)249-28-31  
Владикавказ (8672)28-90-48  
Владимир (4922)49-43-18  
Волгоград (844)278-03-48  
Вологда (8172)26-41-59  
Воронеж (473)204-51-73  
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06  
Ижевск (3412)26-03-58  
Иркутск (395)279-98-46  
Казань (843)206-01-48  
Калининград (4012)72-03-81  
Калуга (4842)92-23-67  
Кемерово (3842)65-04-62  
Киров (8332)68-02-04  
Коломна (4966)23-41-49  
Кострома (4942)77-07-48  
Краснодар (861)203-40-90  
Красноярск (391)204-63-61  
Курск (4712)77-13-04  
Курган (3522)50-90-47  
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13  
Москва (495)268-04-70  
Мурманск (8152)59-64-93  
Набережные Челны (8552)20-53-41  
Нижний Новгород (831)429-08-12  
Новокузнецк (3843)20-46-81  
Ноябрьск (3496)41-32-12  
Новосибирск (383)227-86-73  
Омск (3812)21-46-40  
Орел (4862)44-53-42  
Оренбург (3532)37-68-04  
Пенза (8412)22-31-16  
Петрозаводск (8142)55-98-37  
Псков (8112)59-10-37  
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15  
Рязань (4912)46-61-64  
Самара (846)206-03-16  
Санкт-Петербург (812)309-46-40  
Саратов (845)249-38-78  
Севастополь (8692)22-31-93  
Саранск (8342)22-96-24  
Симферополь (3652)67-13-56  
Смоленск (4812)29-41-54  
Сочи (862)225-72-31  
Ставрополь (8652)20-65-13  
Сургут (3462)77-98-35  
Сыктывкар (8212)25-95-17  
Тамбов (4752)50-40-97  
Тверь (4822)63-31-35

Тольятти (8482)63-91-07  
Томск (3822)98-41-53  
Тула (4872)33-79-87  
Тюмень (3452)66-21-18  
Ульяновск (8422)24-23-59  
Улан-Удэ (3012)59-97-51  
Уфа (347)229-48-12  
Хабаровск (4212)92-98-04  
Чебоксары (8352)28-53-07  
Челябинск (351)202-03-61  
Череповец (8202)49-02-64  
Чита (3022)38-34-83  
Якутск (4112)23-90-97  
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: [pbf@nt-rt.ru](mailto:pbf@nt-rt.ru) || сайт: <https://plas-labs.nt-rt.ru/>